



### Main

Range	Unica
Device application	Power supply
Product or component type	Socket-outlet
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
Socket number	1
Outlet poles configuration	2P
Outlet standard	Euroamerican
Outlet standard description	Without earthing contact

### Complementary

Rated current	16 A, 250 V AC 15 A, 127 V AC
Network frequency	50/60 Hz
Number of modules	1 module
Fixing mode	Clip-in
Colour tint	Ivory
Connections - terminals	Screw terminals
Cable cross section	0...4 mm <sup>2</sup> - cable stiffness: flexible 0...4 mm <sup>2</sup> - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 I <sub>n</sub> and 1.1 I <sub>un</sub> , cos phi: 0.6
Electrical durability	10000 cycles (cos phi: 0.8)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Material	Mechanism cover : ASA + PC
Quantity per set	Blister : set of 1
Product certifications	FR.ME63.B02375 AC
Embedding depth	24 mm
Depth	33 mm
Width	22.5 mm
Height	45 mm
Product weight	0.0206 kg

## Environment

Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Liquid soap Ammonia Alcohol Oil Petrol UV resistant Window-cleaning fluid Acetone Bleach
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0622 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months 18 months
-----------------	---------------------

Product Life Status : **Commercialised**