



Commercial status

End of Commercialisation :

⚠ End of Commercialisation

Main

Range	Unica
Device application	Control
Product or component type	Switch
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
Switch function	2-way
Switch application	Roller blind
Rated current	10 A at 250 V AC 50/60 Hz
Actuator	Push-button
Number of modules	2 modules
Fixing mode	Clip-in
Cover plate colour tint	Ivory

Complementary

Contacts type and composition	1 C/O
Mechanical interlocking	Interlock between up/down
[I _u] rated interrupted current	2.5 A for motor
Opening distance	> 3 mm
Marking	UP Down
Connections - terminals	Screw terminals
Cable cross section	2.5 Mm ² flexible cable 2.5 Mm ² rigid cable
Minimum load breaking capacity	200 operations 1.25 I _n and 1.1 I _u , cos phi = 0.3
Electrical durability	40000 Cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	ASA + PC: mechanism cover
Standards	EMC directive LV directive EN 60669-1
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Embedding depth	21 Mm
Depth	33 Mm
Width	45 Mm

Height	45 Mm
Net weight	0.0381 Kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Acetone Ammonia Bleach Liquid soap Alcohol Petrol Oil Window-cleaning fluid UV resistant
Environmental health and issues	Halogen free

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. - Block**