



Main

Range	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Telephone socket
Device presentation	Mechanism
Colour tint	Ivory
Telephone socket type	British (6 contacts) - category 3 at 16 Mbit/s

Complementary

Socket number	1
Number of modules	1 module
Connections - terminals	Screw terminals twisted pair
Fixing mode	Clip-in
Material	ASA + PC: mechanism cover
Depth	23 Mm
Width	22.5 Mm
Height	45 Mm
Embedding depth	12 Mm
Net weight	0.015 Kg
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Liquid soap Bleach UV resistant Window-cleaning fluid Petrol Ammonia Oil Acetone Alcohol
Environmental health and issues	Halogen free

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**