



### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Plus
Number of gangs	2 gangs
Installation direction	Horizontal
Number of modules	2 x 4 modules
Fixing mode	Screws
Colour tint	Mist grey
Decoration colour	White

### Complementary

Provided equipment	Fixing frame
Material	Cover frame : ABS (acrylonitrile butadiene-styrene) Intermediate part : ASA + PC Fixing frame : LATER 4 G30V0 2307Y1 GRIS
Standards	EN 60669-1
Width	152 mm
Height	155 mm
Depth	16 mm
Distance between centers	47.33 mm
Product weight	0.134 kg

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**