



### Main

Range	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Key card switch
Device application	Control
Device presentation	Mechanism with zamak fixing frame
Cover plate colour tint	Cream (RAL 9010)

### Complementary

[Ue] rated operational voltage	230 V AC +/- 10 % at 50 Hz
Rated current	10 A
Load type	230 V AC incandescent lamp - 1470 W 230 V AC halogen lamp - 1470 W 230 V AC fan - 1470 W 230 V AC convector - 1470 W Low voltage halogen lamp with ferromagnetic transformer - 1000 VA Low voltage halogen lamp with electronic transformer - 1470 VA Fluorescent tube ferromagnetic ballast - 1470 VA Compact fluorescent lamp - 1470 W LED lamp - 1470 W Contactor
Condition of use	Control through appropriate relay
Actuator	Card 54 x 86 x 0.85 mm (maximum)
Number of modules	2 modules
Fuse type	Electronic
Maximum number of switchings	50000 operations
Pilot light	Locator lamp
Marking	Vertical insertion pictogram
Connections - terminals	Soldered connectors
Clamping connection capacity	<= 1 x 2.5 mm <sup>2</sup> for flexible cable(s) <= 1 x 2.5 mm <sup>2</sup> for rigid cable(s)
Fixing mode	Screws
Material	ASA + PC: mechanism cover Zamak: fixing frame
Surface finish	Untreated
Embedding depth	14 Mm
Depth	Unica Basic cover frame: 36 mm Unica Colors cover frame: 36 mm Unica Allegro cover frame: 35 mm Unica Plus cover frame: 35 mm

Width	70.9 Mm
Height	70.9 Mm
Net weight	0.0645 Kg

## Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	5...30 °C
Ambient air temperature for storage	-20...60 °C
Environmental characteristic	Window-cleaning fluid Liquid soap Acetone Ammonia Petrol Bleach Alcohol UV resistant Oil
Environmental health and issues	Halogen free
Product certifications	FR ME63 B02736
Standards	EN 61058-1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. announced**