



Main

Range	Unica
Product or component type	Data socket
Connector type	RCA
Electrical circuit type	Video Audio
Device presentation	Mechanism with zamak fixing frame
Colour tint	Ivory (RAL 9010)
Type of packing	Group

Complementary

Device mounting	Flush
Fixing mode	By screws
Quantity per set	Set of 10
Sale per indivisible quantity	1
Connections - terminals	Screw terminals
Clamping connection capacity	<= 1.5 mm ² stranded <= 1.5 mm ² flexible <= 1.5 mm ² rigid
Wire stripping length	8 mm
Material	Zamak fixing frame PC (polycarbonate) GF10 FR casing Thermoplastic ABS-UV stabilised centre plate
Height	71 mm
Width	71 mm
Depth	28 mm
Embedding depth	19 mm
Product weight	0.075 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...40 °C
IP degree of protection	IP21
IK degree of protection	IK04
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**