



Main

Range of product	Unica Wireless
Product or component type	Combined roller blind
Device presentation	Mechanism with zamak fixing frame + long claws
Transmission frequency	868.3 MHz
[Ue] rated operational voltage	110/230 V AC +/- 10 % at 50/60 Hz
Number of modules	2 modules
Fixing mode	Claws
Colour tint	Aluminium
Device composition	Wireless emitter and receiver 1 large rocker and 2 narrow rockers
Provided equipment	Set of 4 symbols

Complementary

Wiring device mounting	Flush
Operating distance	10...50 m indoor <= 300 m outdoor
Load type	Motor: 690 W
Protection type	Fuse protection
Connections - terminals	Screw terminals
Clamping connection capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Type of setting	Neutral position
Standards	EN 60669-2-1 99/5/EEC ETSI EN 300 220 89/336/EEC EN 60669-1 ETSI EN 301 489
Ambient air temperature for operation	-5...50 °C
Relative humidity	20...95 %
Embedding depth	34 Mm
Depth	46 Mm

Environment

IP degree of protection	IP20
Environmental characteristic	Acetone UV resistant Liquid soap Ammonia Petrol Oil Bleach Alcohol Window-cleaning fluid
Environmental health and issues	Halogen free

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. announced**