



### Main

Range	Unica
Device application	Signalling
Product or component type	Electronic bell
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism with zamak fixing frame
[Ue] rated operational voltage	230 V AC 50/60 Hz
Number of modules	2 modules
Fixing mode	Screws
Colour tint	White (RAL 9003)

### Complementary

Current consumption	14 mA
Type of setting	5 programmable melodies
Device mounting	Flush
Connections - terminals	Screw terminals
Acoustic level	70 dB/1m
Cable cross section	0.75...1.5 Mm <sup>2</sup> flexible cable 0.75...1.5 Mm <sup>2</sup> rigid cable
Connected auxiliaries	3 indicator lights connected in parallel 10 standard push-buttons connected in parallel
Material	ASA + PC: mechanism cover Zamak: fixing frame
Standards	IEC 62080
Product certifications	CE
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	33 Mm
Depth	44 Mm
Width	45 Mm
Height	45 Mm
Net weight	0.1489 Kg

## Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Liquid soap Alcohol Ammonia Window-cleaning fluid Acetone Oil Petrol Bleach UV resistant
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**