



Main

Range	Unica
Device application	Signalling
Product or component type	Electronic bell
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism with zamak fixing frame
[Ue] rated operational voltage	230 V AC 50/60 Hz
Number of modules	2 modules
Fixing mode	Screws
Colour tint	Ivory (RAL 9010)

Complementary

Current consumption	14 mA
Type of setting	5 programmable melodies
Device mounting	Flush
Connections - terminals	Screw terminals
Acoustic level	70 dB/1m
Cable cross section	0.75...1.5 Mm ² flexible cable 0.75...1.5 Mm ² rigid cable
Connected auxiliaries	10 standard push-buttons connected in parallel 3 indicator lights connected in parallel
Material	ASA + PC: mechanism cover Zamak: fixing frame
Standards	IEC 62080
Product certifications	CE
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	33 Mm
Depth	44 Mm
Width	45 Mm
Height	45 Mm
Net weight	0.1489 Kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Oil Petrol UV resistant Bleach Acetone Window-cleaning fluid Ammonia Liquid soap Alcohol
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**