



Main

Range	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Telephone socket
Device presentation	Mechanism with zamak fixing frame + long claws
Colour tint	White
Telephone socket type	RJ11 (4 contacts) - category 3 at 16 Mbit/s

Complementary

Socket number	1
Number of modules	2 modules
Connections - terminals	Screw terminals twisted pair
Fixing mode	Long claws
Material	ASA + PC: mechanism cover Zamak: fixing frame
Depth	23 Mm
Width	27 Mm
Height	29 Mm
Embedding depth	12 Mm
Net weight	0.055 Kg
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Oil Liquid soap Ammonia Window-cleaning fluid Acetone Petrol UV resistant Bleach Alcohol
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**