



Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Range	Unica
Aesthetic name	Unica Top - Unica Class
Product or component type	Telephone socket
Device presentation	Mechanism with zamak fixing frame + long claws
Colour tint	Graphite
Telephone socket type	RJ12 (6 contacts) - category 3 at 16 Mbit/s

Complementary

Socket number	1
Number of modules	2 modules
Connections - terminals	Screw terminals twisted pair
Fixing mode	Long claws
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover Zamak: fixing frame
Depth	23 Mm
Width	45 Mm
Height	45 Mm
Embedding depth	12 Mm
Net weight	0.057 Kg
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Bleach Alcohol Acetone Oil Ammonia Liquid soap Window-cleaning fluid UV resistant Petrol
Environmental health and issues	Halogen free

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	End of commerc. - Block
-----------------------	-------------------------