



Main

Range	Unica
Accessory / separate part category	Cabling accessory
Product or component type	Cable outlet
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism with zamak fixing frame + long claws
Number of modules	2 modules
Fixing mode	Long claws
Provided equipment	Anti-tug clamps
Colour tint	Ivory (RAL 9010)

Complementary

Rated current	16 A
Connections - terminals	Screw terminals
Clamping connection capacity	<= 3 x 2.5 mm ² for flexible cable(s) <= 3 x 2.5 mm ² for rigid cable(s)
Material	ASA + PC: mechanism cover Zamak: fixing frame
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Width	70.9 Mm
Height	70.9 Mm
Net weight	0.0567 Kg

Environment

IK degree of protection	IK01
IP degree of protection	IP40
Environmental characteristic	Acetone Liquid soap Window-cleaning fluid Bleach Oil Petrol UV resistant Ammonia Alcohol
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**