



### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Top
Number of gangs	2 gangs vertical
Fixing mode	Clip-in
Cover frame colour tint	Glossy chrome
Decoration colour	Graphite

### Complementary

Material	ASA + PC: intermediate part Zamak: cover frame
Standards	EN 60669-1
Height	147 Mm
Width	80 Mm
Depth	14 Mm
Distance between centers	57 Mm
Net weight	0.078 Kg

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Oil UV resistant Ammonia Bleach Acetone Alcohol Liquid soap Petrol Window-cleaning fluid
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**