



Main

Range	Mini Pragma
Product or component type	Enclosure
Enclosure type	Modular enclosure
Number of 18 mm modules per row	18
Number of horizontal rows	1
Type of front cover	Translucid
Width	376 mm outside
Height	228 mm outside
Depth	103 mm outside

Complementary

Enclosure mounting	Surface
9 mm pitches	36
Total number of 18 mm modules	18
[In] rated current	63 A
Type of rail	35 mm asymmetrical rail
Cable entry	1 bare flange 1 trunking flange
Terminal block function	Without
Enclosure material	Back part : technoplastic Door : technoplastic Front face : technoplastic
Colour	Front face : white (RAL 9003) Door : translucid

Environment

Standards	EN 50102 IEC 529 IEC 60439-3 IEC 60670-24 IEC 60695-2-11
Quality labels	IMQ
Fire resistance	Door : 650 °C Front face : 650 °C Back part : 650 °C
IP degree of protection	IP40
IK degree of protection	IK07
Ambient air temperature for operation	-25...60 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0901 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**