



### Main

Range	Mini Pragma
Product or component type	Enclosure
Enclosure type	Modular enclosure
Number of 18 mm modules per row	6
Number of horizontal rows	1
Type of front cover	Plain
Width	162 mm wall 186 mm outside
Height	228 mm wall 252 mm outside
Depth	98 mm total 18 mm outside 80 mm wall
Embedding depth	80 mm

### Complementary

Enclosure mounting	Flush
9 mm pitches	12
Total number of 18 mm modules	6
[In] rated current	63 A
Type of rail	35 mm asymmetrical rail
Cable entry	Pre-cutted holes
Terminal block function	Without
Enclosure material	Back part : technoplastic Door : technoplastic Front face : technoplastic
Colour	Door : white ( RAL 9003 ) Front face : white ( RAL 9003 )

## Environment

Standards	EN 50102 IEC 529 IEC 60439-3 IEC 60670-24 IEC 60695-2-11
Quality labels	IMQ
Fire resistance	Door : 650 °C Front face : 650 °C Back part : 650 °C
IP degree of protection	IP40
IK degree of protection	IK07
Ambient air temperature for operation	-25...60 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0901 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**