



### Main

Range of product	EasyPact MVS
Range	EasyPact
Product or component type	Switch disconnecter
Device application	Distribution
Poles description	4P
Neutral position	Left
Network type	AC
Breaking capacity code	NA
Suitability for isolation	Yes conforming to IEC 60947-3
Utilisation category	AC-23A

### Complementary

Network frequency	50/60 Hz
Control type	Push-button
Mounting mode	Drawout
Mounting support	Rail
Connection position	Vertical Horizontal
Location of connection	Rear
[Ie] rated operational current	AC-23A: 4000 A AC 50/60 Hz 690 V
Rated duty	Continuous
[Ui] rated insulation voltage	1000 V AC 50/60 Hz conforming to IEC 60947-3
[Uimp] rated impulse withstand voltage	12 KV conforming to IEC 60947-3
[Icw] rated short-time withstand current	55 KA during 1 s conforming to IEC 60947-3 at -5...70 °C 30 KA during 3 s conforming to IEC 60947-3 at -5...70 °C
[Icm] rated short-circuit making capacity	121 KA AC at 50/60 Hz
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-3
Contact position indicator	Yes
Mechanical durability	20000 Cycles with maintenance conforming to IEC 60947-3 10000 Cycles without maintenance conforming to IEC 60947-3
Electrical durability	AC-23A: 5000 cycles 440 V AC 50/60 Hz without maintenance conforming- to IEC 60947-3 AC-23A: 2500 cycles 690 V AC 50/60 Hz without maintenance conforming- to IEC 60947-3
Connection pitch	115 Mm without spreader
Height	439 Mm
Width	556 Mm
Depth	395 Mm
Net weight	120 Kg

## Environment

Standards	IEC 60947-3
Product certifications	CCC IEC CCS GOST
IP degree of protection	IP40
Pollution degree	4 conforming to IEC 60664-1
Ambient air temperature for operation	-5...70 °C
Ambient air temperature for storage	-40...85 °C without control unit

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**