



Main

Product or component type	Socket-outlet
Socket number	2
Outlet standard	Italian
Outlet poles configuration	2P + E
Device presentation	Complete product
Colour tint	White

Complementary

Device mounting	Flush
Number of modules	2 modules
Rated current	10 A at 250 V AC 50/60 Hz
Fixing mode	Clip-in
Material	PC (polycarbonate)
Surface finish	Glossy
Connections - terminals	Screw clamp terminal
AWG gauge	AWG 12
Width	113 Mm
Height	75 Mm
Depth	31 Mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**