



Main

Range	Evlink
Product or component type	Simulation tool

Complementary

Earthing system	TN TT
Output type	Socket-inlet T2 right 400 V Socket-inlet T1 left 230 V
Height	270 Mm
Width	305 Mm
Depth	170 Mm
Product weight	6 Kg
Colour	Black

Environment

Standards	IEC 61851-1 IEC 61010-1
IP degree of protection	IP44 (opened) IP54 (closed)
IK degree of protection	IK08
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-30...50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	5.489 Kg
Package 1 Height	20 Cm
Package 1 width	28.2 Cm
Package 1 Length	39 Cm
Unit Type of Package 2	P12
Number of Units in Package 2	24
Package 2 Weight	146.088 Kg
Package 2 Height	74 Cm
Package 2 width	80 Cm
Package 2 Length	120 Cm

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Product Life Status : **Commercialised**