



Main

Range of product	Actassi
Product or component type	Fixed slide
Accessory / separate part category	Support accessory
Quantity per set	Set of 2

Complementary

Range compatibility	Actassi VDA Actassi VDS
Material	Treated steel
Mounting location	Upright
Number of rack unit	38U 42U 29U 47U 24U 33U
Depth	800 mm : rack 1000 mm : rack
Fixing mode	Direct fixing: upright
Permanent permissible load	60 kg
Distance between centers	458 mm
Distance between cable supports	550 m

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.