

Main

Range of product	Celleen
Product or component type	Mounting plate
Device short name	NSY
Type of front plate	Windowed
Product specific application	To mount device on disconnectable mounting plate
Sale per indivisible quantity	1

Complementary

Product destination	Variable speed drive
Installed device	1 ATV212 at 37...45 kW (vertical)
Height	800 mm
Width	600 mm
Material	Galvanized steel

Environment

Standards	EN/IEC 61439-1
Product certifications	ASEFA

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.