



Main

Range	Spacial
Offer type	Spare part
Accessory / separate part category	Enclosure accessory
Product or component type	Roof
Device application	Multi-purpose
Enclosure nominal dimensions	D: 700 mm
Mounting location	On top of enclosure
Range compatibility	Spacial Spacial SF suitable enclosure
Device composition	1 roof

Complementary

Material	Steel
Colour	Grey RAL 7035
Surface finish	Epoxy-polyester powder
Fixing mode	By screws - screw type M6 - roof fixing point location By screws - screw type M12 - roof fixing point location
Height	7.5 mm
Width	696 mm
Depth	596 mm
Thickness	1.5 mm
IP degree of protection	IP55 enclosure protection conforming to IEC 60529

Product Life Status : **Commercialised**