



Main

Range	New Unica
Product or component type	Workstation
Number of modules	2 x 4 modules
Fixing mode	Screws
Colour tint	Aluminium

Complementary

Provided equipment	Fixing frame Cover frame
Device mounting	Surface
Cable entry	3 removable plates Knock-outs 20 mm for diameter 1 bottom cable entry 20 mm for diameter 1 bottom cable entry 30 mm for diameter 1 bottom cable entry 40 mm for diameter 1 bottom cable entry 25 mm for diameter
Material	Cover frame : ABS (acrylonitrile butadiene-styrene) Box : ABS (acrylonitrile butadiene-styrene) Separator : ABS (acrylonitrile butadiene-styrene)
Depth	60 mm
Width	165 mm
Height	165 mm
Product weight	0.379 kg

Environment

IK degree of protection	IK04
Environmental characteristic	Liquid soap Ammonia Bleach Petrol Alcohol Window-cleaning fluid UV resistant Oil Acetone
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.