



Main

Range	New Unica
Product or component type	Workstation
Number of modules	3 x 4 modules
Fixing mode	Claws Embedment
Colour tint	White (RAL 9003)

Complementary

Provided equipment	Fixing frame Cover frame
Device mounting	Flush
Cable entry	6 knock-outs 20 mm for diameter 6 knock-outs 25 mm for diameter 2 bottom cable entries 45 x 25 mm for size 20 mm for diameter 4 bottom cable entries 50 x 35 mm for size 25 mm for diameter
Fire resistance	850 °C @<= 30 s
Material	Cover frame : ABS (acrylonitrile butadiene-styrene) Separator : ABS (acrylonitrile butadiene-styrene) Box : PC
Depth	62 mm
Width	230 mm
Height	165 mm
Product weight	0.401 kg

Environment

IK degree of protection	IK04
Environmental characteristic	Window-cleaning fluid Petrol Ammonia Alcohol Oil Acetone UV resistant Liquid soap Bleach
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**