

Main

Range	New Unica
Range of product	New Unica
Product or component type	Workstation
Product compatibility	Unica
Number of modules	4 x 4 modules
Fixing mode	Claws Embedment
Colour tint	Aluminium

Complementary

Provided equipment	Cover frame Fixing frame
Device mounting	Flush
Cable entry	8 knock-outs 20 mm for diameter 8 knock-outs 25 mm for diameter 4 bottom cable entries 50 x 35 mm for size 25 mm for diameter 4 bottom cable entries 50 x 35 mm for size 20 mm for diameter
Fire resistance	850 °C @ ≤ 30 s
Material	Cover frame : ABS (acrylonitrile butadiene-styrene) Separator : ABS (acrylonitrile butadiene-styrene) Box : PC
Depth	62 mm
Width	300 mm
Height	165 mm
Product weight	0.514 kg
Targeted channel	Professional
Main colour tint	Aluminium

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IK degree of protection	IK04
Environmental characteristic	Window-cleaning fluid Oil Liquid soap Acetone UV resistant Alcohol Petrol Bleach Ammonia
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**