



Main

Range	New Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Studio Metal
Number of gangs	3 gangs
Installation direction	Horizontal/Vertical
Type of frame	Triple
Number of modules	3 x 2 modules
Fixing mode	Clip-in
Colour tint	Bronze
Decoration colour	Beige (RAL 1013)

Complementary

Material	Thermoplastic ABS-UV stabilised: cover frame Polycarbonate: intermediate plate
Standards	IEC 60884-1 IEC 60669-1
Width	227 Mm
Height	85 Mm
Depth	10 Mm
Net weight	0.047 Kg

Environment

IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Oil Bleach Ammonia UV resistant Alcohol Petrol Liquid soap Window-cleaning fluid Acetone
Environmental health and issues	Halogen free

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Product Life Status : **Commercialised**