



Main

Range of product	New Unica
Range	New Unica
Device application	Power supply
Product or component type	Socket-outlet
Device presentation	Mechanism
Socket number	1
Outlet poles configuration	2P + E with shutters
Outlet standard	French
Outlet standard description	Pin earth

Complementary

Main colour tint	Aluminium
Rated current	16 A, 250 V AC
Network frequency	50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Aluminium
Connections - terminals	Screw terminals
Cable cross section	0...4 mm ² cable(s), 2 - cable stiffness: flexible 0...4 mm ² cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi: 0.6
Electrical durability	10000 cycles (cos phi: 0.8)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Material	Mechanism cover : PC
Surface finish	Brilliant
Quantity per set	Flow-pack : set of 1
Standards	IEC 60884-1 NF C 61-314
Product certifications	NF
Embedding depth	27.4 mm
Depth	37 mm
Width	45 mm
Height	45 mm
Product weight	0.031 kg
Surface treatment	Painted
Targeted channel	Professional

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Bleach Acetone Liquid soap Ammonia Window-cleaning fluid UV resistant Petrol Alcohol Oil
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**