



Main

Range	New Unica
Device application	Power supply
Product or component type	Socket-outlet
Device presentation	Mechanism
Socket number	2
Outlet poles configuration	2P + E with shutters
Outlet standard	French
Outlet standard description	Pin earth
Ground lug position	45° ground lug

Complementary

Rated current	16 A, 250 V AC
Network frequency	50/60 Hz
Number of modules	4 modules
Fixing mode	Clip-in
Colour tint	White (RAL 9003)
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² cable(s), 2 - cable stiffness: flexible 0...2.5 mm ² cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 I _n and 1.1 I _{un} , cos phi: 0.6
Electrical durability	10000 cycles (cos phi: 0.8)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Material	Mechanism cover : PC
Surface finish	Glossy
Quantity per set	Without packaging : set of 1
Standards	IEC 60884-1 NF C 61-314
Product certifications	NF
Embedding depth	30 mm
Depth	39.4 mm
Width	45 mm
Height	90 mm
Product weight	0.075 kg
Surface treatment	Untreated

Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Window-cleaning fluid Ammonia Alcohol UV resistant Bleach Oil Petrol Liquid soap
Environmental health and issues	Halogen free

Offer Sustainability

REACH	Reference not containing SVHC above the threshold
-------	---

Product Life Status : **Commercialised**