

Main

Range of product	New Unica
Range	New Unica
Device application	Power supply
Product or component type	Socket-outlet
Device presentation	Mechanism
Socket number	3
Outlet poles configuration	2P + E with shutters
Outlet standard	French
Outlet standard description	Pin earth
Ground lug position	45° ground lug

Complementary

Main colour tint	Red
Rated current	16 A, 250 V AC
Network frequency	50/60 Hz
Number of modules	6 modules
Fixing mode	Clip-in
Colour tint	Red
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² cable(s), 2 - cable stiffness: flexible 0...2.5 mm ² cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi: 0.6
Electrical durability	10000 cycles (cos phi: 0.8)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Material	Mechanism cover : PC
Surface finish	Glossy
Quantity per set	Without packaging : set of 1
Standards	IEC 60884-1 NF C 61-314
Product certifications	NF
Embedding depth	30 mm
Depth	39.4 mm
Width	45 mm
Height	135 mm
Product weight	0.106 kg

Surface treatment	Antibacterial
Targeted channel	Professional

Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Alcohol Oil Bleach Window-cleaning fluid UV resistant Acetone Petrol Liquid soap Ammonia
Environmental health and issues	Halogen free

Offer Sustainability

REACH	Reference not containing SVHC above the threshold
-------	---

Product Life Status :	Commercialised
-----------------------	-----------------------