



Main

Range of product	New Unica
Range	New Unica
Device application	Bell switch
Product or component type	Push-button switch
Device presentation	Mechanism
Colour tint	White (RAL 9003)
Quantity per set	10 flow-pack

Complementary

Rated current	10 A, 250 V AC, 50/60 Hz
Electrical durability	20000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Pilot light	Without LED :
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible)
Material	Casing : PC (polycarbonate) GF10 FR Mechanism rocker : thermoplastic ABS-UV stabilised Terminals : CuZn37 Release button : PBT (polybutylene terephthalate) GF30
Marking	Bell symbol
Surface finish	Glossy
Fixing mode	Clip-in
Width	45 mm
Height	45 mm
Depth	34.25 mm
Embedding depth	21.15 mm
Product weight	0.0175 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C
Standards	IEC 60669-1 RoHS compliant LV directive

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Product certifications	Aenor CE EAC NF
Targeted channel	Professional
Main colour tint	White

Environment

IP degree of protection	IP21D
IK degree of protection	IK04
Environmental characteristic	Alcohol Acetone Liquid soap Window-cleaning fluid Bleach UV resistant Oil Petrol Ammonia
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**