



### Main

Range	New Unica
Product or component type	USB charger
Device presentation	Mechanism

### Complementary

Device application	Charger
Number of modules	2 modules
Colour tint	White (RAL 9003)
[Ue] rated operational voltage	100...240 V AC 50/60 Hz
Input power	7.5 W
Socket number	2
Integrated connection type	2 USB type A 5 V DC, maximum load current: 1 A
Material	Centre plate : thermoplastic ABS-UV stabilised Casing : PC (polycarbonate) GF10 FR Internal cover : PC (polycarbonate) GF10 FR
Protection type	Short-circuit protection
Number of terminals	2 screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1.5...2.5 mm <sup>2</sup> rigid 1.5...2.5 mm <sup>2</sup> flexible
Wire stripping length	8 mm
Product compatibility	All devices fulfilling the EN 62684 standard
Fixing mode	Clip-in
Type of packing	Flow-pack
Ambient air temperature for operation	5...45 °C
Ambient air temperature for storage	-5...50 °C
Standards	IEC 62368-1 IEC 62680-3 EN 61000-6-3 EN 61000-6-1
Height	75 mm
Width	75 mm
Depth	39 mm
Embedding depth	27 mm
Product weight	0.082 kg

## Environment

Electrical insulation class	Class II
Environmental characteristic	Bleach Acetone Oil Petrol Liquid soap Window-cleaning fluid Alcohol UV resistant Ammonia
IK degree of protection	IK04
IP degree of protection	IP2xC

Product Life Status : **Commercialised**