



### Main

Range	New Unica
Product or component type	Audio/Video socket
Connector type	HDMI
Electrical circuit type	Audio/Video
Device presentation	Mechanism
Colour tint	Aluminium
Type of packing	Flow-pack

### Complementary

Fixing mode	Clip-in
Number of modules	1 module
Surface finish	Brilliant
Quantity per set	Set of 10
Sale per indivisible quantity	1
Material	Thermoplastic ABS-UV stabilised: centre plate
Height	45 Mm
Width	22.5 Mm
Depth	220 Mm
Net weight	0.036 Kg

### Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 50157 EN 50049
IP degree of protection	IP2xC
IK degree of protection	IK02
Environmental characteristic	Bleach Oil Alcohol Ammonia Window-cleaning fluid UV resistant Petrol Acetone Liquid soap
Environmental health and issues	Halogen free

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**