



Main

Range	New Unica
Product or component type	Video socket
Connector type	VGA
Electrical circuit type	Video
Device presentation	Mechanism
Colour tint	Anthracite (RAL 7021)
Type of packing	Flow-pack

Complementary

Fixing mode	Clip-in
Number of modules	1 module
Surface finish	Matt
Quantity per set	Set of 10
Sale per indivisible quantity	1
Material	Thermoplastic ABS-UV stabilised centre plate
Height	45 mm
Width	22.5 mm
Depth	220 mm
Product weight	0.054 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
IP degree of protection	IP2xC
IK degree of protection	IK02
Environmental characteristic	Acetone Ammonia Liquid soap Window-cleaning fluid Bleach Petrol UV resistant Oil Alcohol
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**