



### Main

Range	New Unica
Product or component type	TV/FM/SAT socket
Device application	Communication Media device support
Device presentation	Mechanism
TV socket type	Intermediate
Colour tint	Anthracite (RAL 7021)

### Complementary

TV connector	Male IEC 9.52 mm
SAT connector	Female IEC 9.52 mm
Path attenuation	11.5 DB R-TV signal5...862 MHz 11.5 DB SAT signal950...2200 MHz 2.5 DB IN-OUT signal47...2150 MHz
DC current flow	Yes
Number of modules	2 modules
Material	Thermoplastic ABS-UV stabilised: central plate
Surface finish	Painted powder coated
Marking	With imprint
Device mounting	Flush
Fixing mode	Clip-in
Depth	33 Mm
Width	45 Mm
Height	45 Mm
Embedding depth	33 Mm

### Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-25...55 °C
Environmental characteristic	UV resistant Ammonia Acetone Petrol Oil Liquid soap Window-cleaning fluid Alcohol Bleach

Environmental health and issues	Halogen free
Standards	CE

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status :	<b>Commercialised</b>
-----------------------	-----------------------