



## Main

Range	New Unica
Device application	Safety
Product or component type	Fuse holder
Device presentation	Mechanism
Rated current	16 A, 230 V AC, 50/60 Hz
Number of modules	1 module
Fixing mode	Clip-in
Colour tint	Aluminium

## Complementary

Fuse type	Cylindrical (8.3 x 31.5 mm)
Provided equipment	Fuse not supplied
Connections - terminals	Screw terminals
Cable cross section	0...4 mm <sup>2</sup> (rigid) 0...4 mm <sup>2</sup> (flexible)
Material	Casing : PC (polycarbonate) GF10 FR Mechanism cover : thermoplastic ABS-UV stabilised
Standards	EN 60269
Ambient air temperature for operation	5...45 °C
Ambient air temperature for storage	-5...50 °C
Embedding depth	31 mm
Depth	44 mm
Width	22.5 mm
Height	45 mm
Product weight	0.024 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

IK degree of protection	IK02
IP degree of protection	IP2xC
Environmental characteristic	Oil Liquid soap Acetone Petrol Window-cleaning fluid UV resistant Ammonia Bleach Alcohol
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**