



### Main

Range	New Unica
Product or component type	Light module
Device presentation	Mechanism
[Ue] rated operational voltage	12...24 V DC
Number of modules	1 module
Fixing mode	Clip-in

### Complementary

Input power	0.2 W
Light block colour	White
Bulb type	LED
Connections - terminals	Screw terminals
Clamping connection capacity	<= 2 x 2.5 mm <sup>2</sup> for flexible cable(s) <= 2 x 2.5 mm <sup>2</sup> for rigid cable(s)
Material	Casing : PC (polycarbonate) GF10 FR Mechanism cover : PC
Standards	CE EN 62094-1
Directives	2014/35/EU - low voltage directive
Ambient air temperature for operation	5...45 °C
Ambient air temperature for storage	-5...50 °C
Embedding depth	21 mm
Depth	31 mm
Width	22.5 mm
Height	45 mm
Product weight	0.018 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

IK degree of protection	IK03
IP degree of protection	IP2xC
Environmental characteristic	Petrol Oil Liquid soap Acetone Alcohol Window-cleaning fluid Bleach UV resistant Ammonia
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**