



Main

Range	New Unica
Product or component type	Emergency light
Device presentation	Mechanism
[Ue] rated operational voltage	230 V AC (+/- 10 %), 50 Hz
Number of modules	2 modules
Fixing mode	Clip-in

Complementary

Condition of use	Battery and bulb cannot be replaced
Light block colour	Green
Bulb type	LED
Bulb lifespan	400 h
Illuminance	45 lux 25 cm
Connections - terminals	Screw terminals
Clamping connection capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Charging time	24 h
Electrical durability	500 cycles
Material	Casing : PC (polycarbonate) GF10 FR Mechanism cover : PC
Standards	EN 60598-2-22 CE
Directives	2014/35/EU - low voltage directive
Ambient air temperature for operation	5...45 °C
Ambient air temperature for storage	-5...50 °C
Embedding depth	32 mm
Depth	43 mm
Width	45 mm
Height	45 mm
Product weight	0.085 kg
Targeted channel	Professional

Environment

IK degree of protection	IK03
IP degree of protection	IP2xC
Environmental characteristic	Oil Liquid soap Window-cleaning fluid UV resistant Ammonia Acetone Alcohol Petrol Bleach
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**