

Main

Range of product	New Unica
Range	New Unica
Product or component type	USB charger
Device presentation	Mechanism with fixing frame
Output current	2.4 A

Complementary

Device application	Charger
Device mounting	Flush
Number of modules	2 modules
Colour tint	White (RAL 9003)
[Ue] rated operational voltage	100...240 V AC 50/60 Hz
Power consumption in W	<= 0.075 W
Nominal output power	12 W
Input power	12 W
Service life in hours	30000 h 12 W
Socket number	2
Integrated connection type	1 USB type A 5 V DC, maximum load current: 2.4 A 1 USB type C 5 V DC, maximum load current: 2.4 A
Material	Casing : PC (polycarbonate) GF10 FR Internal cover : PC (polycarbonate) GF10 FR Centre plate : ABS (acrylonitrile butadiene-styrene)
Protection type	Short-circuit protection
Number of terminals	2 screw terminals
Clamping connection capacity	2 x 0.75...2 x 2.5 mm ² rigid 2 x 0.75...2 x 2.5 mm ² flexible 2 x 0.75...2 x 2.5 mm ² stranded
Wire stripping length	8 mm
Product compatibility	All devices fulfilling the EN 62684 standard
Fixing mode	By claws By screws
Type of packing	Flow-pack
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-5...50 °C
Standards	EN 62684 ETSI EN 301 489-4 EN 60950-1
Height	45 mm
Width	22.5 mm

Depth	42 mm
Embedding depth	30.8 mm
Targeted channel	Professional
Main colour tint	White

Environment

Electrical insulation class	Class II
Environmental characteristic	REACH Regulation (EC) No 1907/2006
IK degree of protection	IK04
IP degree of protection	IP20

Product Life Status : **Commercialised**