

### Main

Range of product	New Unica
Range	New Unica
Product or component type	USB charger
Device presentation	Mechanism with fixing frame
Output current	2.4 A

### Complementary

Device application	Charger
Device mounting	Flush
Number of modules	2 modules
Colour tint	Beige (RAL 1013)
[Ue] rated operational voltage	100...240 V AC 50/60 Hz
Power consumption in W	<= 0.075 W
Nominal output power	12 W
Input power	12 W
Service life in hours	30000 h 12 W
Socket number	2
Integrated connection type	1 USB type A 5 V DC, maximum load current: 2.4 A 1 USB type C 5 V DC, maximum load current: 2.4 A
Material	Casing : PC (polycarbonate) GF10 FR Internal cover : PC (polycarbonate) GF10 FR Centre plate : ABS (acrylonitrile butadiene-styrene)
Protection type	Short-circuit protection
Number of terminals	2 screw terminals
Clamping connection capacity	2 x 0.75...2 x 2.5 mm <sup>2</sup> rigid 2 x 0.75...2 x 2.5 mm <sup>2</sup> flexible 2 x 0.75...2 x 2.5 mm <sup>2</sup> stranded
Wire stripping length	8 mm
Product compatibility	All devices fulfilling the EN 62684 standard
Fixing mode	By claws By screws
Type of packing	Flow-pack
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-5...50 °C
Standards	EN 60950-1 EN 62684 ETSI EN 301 489-4
Height	45 mm
Width	22.5 mm

Depth	42 mm
Embedding depth	30.8 mm
Targeted channel	Professional
Main colour tint	Beige

### Environment

Electrical insulation class	Class II
Environmental characteristic	REACH Regulation (EC) No 1907/2006
IK degree of protection	IK04
IP degree of protection	IP20

Product Life Status : **Commercialised**