



## Main

Range	New Unica
Device application	Power supply
Product or component type	Socket-outlet
Device presentation	Mechanism with zamak fixing frame
Socket number	1
Outlet poles configuration	2P + E
Outlet standard	German
Outlet standard description	Side earth

## Complementary

Rated current	16 A, 250 V AC
Network frequency	50/60 Hz
Number of modules	2 modules
Fixing mode	Screws or claws
Colour tint	Anthracite (RAL 7021)
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm <sup>2</sup> cable(s), 2 - cable stiffness: flexible 0...2.5 mm <sup>2</sup> cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 I <sub>n</sub> and 1.1 I <sub>un</sub> , cos phi: 0.6
Electrical durability	10000 cycles (cos phi: 0.8)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Material	Mechanism cover : PC
Surface finish	Matt
Quantity per set	Flow-pack : set of 1
Standards	IEC 60884-1 DIN VDE 0620-1
Product certifications	EAC
Embedding depth	32 mm
Depth	42 mm
Width	70.9 mm
Height	70.9 mm
Product weight	0.0645 kg
Surface treatment	Painted

## Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP20
Environmental characteristic	Petrol UV resistant Liquid soap Oil Acetone Bleach Window-cleaning fluid Ammonia Alcohol
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**