

Main

| | |
|-----------------------------|-----------------------------------|
| Range of product | New Unica |
| Range | New Unica |
| Device application | Power supply |
| Product or component type | Socket-outlet |
| Device presentation | Mechanism with zamak fixing frame |
| Socket number | 1 |
| Outlet poles configuration | 2P + E with shutters |
| Outlet standard | German |
| Outlet standard description | Side earth |

Complementary

| | |
|--------------------------------|---|
| Main colour tint | White |
| Rated current | 16 A, 250 V AC |
| Network frequency | 50/60 Hz |
| Number of modules | 2 modules |
| Fixing mode | Screws or claws |
| Colour tint | White (RAL 9003) |
| Connections - terminals | Screwless terminals |
| Cable cross section | 0...2.5 mm ² cable(s), 2 - cable stiffness: flexible 0...2.5 mm ² cable(s), 2 - cable stiffness: rigid |
| Minimum load breaking capacity | 100 operations 1.25 In and 1.1 Un, cos phi: 0.6 |
| Electrical durability | 10000 cycles (cos phi: 0.8) |
| Insulation resistance | > 5 MOhm @500 V |
| Dielectric strength | 2000 V |
| Material | Mechanism cover : PC |
| Surface finish | Glossy |
| Quantity per set | Flow-pack : set of 1 |
| Standards | IEC 60884-1 DIN VDE 0620-1 UNE 20315-1-1 UNE 20315-1-2 |
| Product certifications | Aenor EAC |
| Embedding depth | 32 mm |
| Depth | 42 mm |
| Width | 70.9 mm |
| Height | 70.9 mm |
| Product weight | 0.0645 kg |

| | |
|-------------------|--------------|
| Surface treatment | Untreated |
| Targeted channel | Professional |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for operation | -5...35 °C |
| Ambient air temperature for storage | -5...50 °C |
| IK degree of protection | IK04 |
| IP degree of protection | IP21D |
| Environmental characteristic | Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid |
| Environmental health and issues | Halogen free |

Offer Sustainability

| | |
|-------|---|
| REACH | Reference not containing SVHC above the threshold |
|-------|---|

Product Life Status : **Commercialised**