



### Main

Range	New Unica
Product or component type	USB data connector
Connector type	USB 2.0
Electrical circuit type	Data
Device presentation	Mechanism with zamak fixing frame
Colour tint	Aluminium
Type of packing	Flow-pack

### Complementary

Fixing mode	Screws or claws
Number of modules	2 modules
Surface finish	Brilliant
Quantity per set	Set of 10
Sale per indivisible quantity	1
Connections - terminals	Screw terminals
Clamping connection capacity	<= 1.5 mm <sup>2</sup> for flexible cable(s) <= 1.5 mm <sup>2</sup> for rigid cable(s)
Wire stripping length	8 Mm
Material	Thermoplastic ABS-UV stabilised: centre plate PC (polycarbonate) GF10 FR: casing Zamak: fixing frame
Height	74.5 Mm
Width	74.5 Mm
Depth	28 Mm
Embedding depth	19.7 Mm
Net weight	0.06 Kg
Directives	2014/30/EU - electromagnetic compatibility

### Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 62680-2-1 EN 61000-6-3 EN 61000-6-1
IP degree of protection	IP2xC
IK degree of protection	IK02

Environmental characteristic	Oil Alcohol Liquid soap Ammonia Petrol Acetone Window-cleaning fluid UV resistant Bleach
Environmental health and issues	Halogen free

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**