



### Main

Range	New Unica
Product or component type	USB data connector
Connector type	USB 2.0
Electrical circuit type	Data
Device presentation	Mechanism with zamak fixing frame
Colour tint	Anthracite (RAL 7021)
Type of packing	Flow-pack

### Complementary

Fixing mode	Screws or claws
Number of modules	2 modules
Surface finish	Matt
Quantity per set	Set of 10
Sale per indivisible quantity	1
Connections - terminals	Screw terminals
Clamping connection capacity	<= 1.5 mm <sup>2</sup> flexible <= 1.5 mm <sup>2</sup> rigid
Wire stripping length	8 mm
Material	Zamak fixing frame PC (polycarbonate) GF10 FR casing Thermoplastic ABS-UV stabilised centre plate
Height	75 mm
Width	75 mm
Depth	28 mm
Embedding depth	19.7 mm
Product weight	0.06 kg
Directives	2014/30/EU - electromagnetic compatibility
Targeted channel	Professional

### Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 61000-6-3 EN 62680-2-1 EN 61000-6-1
IP degree of protection	IP2xC
IK degree of protection	IK02

Environmental characteristic	Ammonia Acetone Bleach Window-cleaning fluid UV resistant Oil Petrol Liquid soap Alcohol
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**