



Main

| | |
|---------------------------|-----------------------------------|
| Range | New Unica |
| Product or component type | Audio/Video socket |
| Connector type | HDMI |
| Electrical circuit type | Audio/Video |
| Device presentation | Mechanism with zamak fixing frame |
| Colour tint | Aluminium |
| Type of packing | Flow-pack |

Complementary

| | |
|-------------------------------|--|
| Fixing mode | Screws or claws |
| Number of modules | 2 modules |
| Surface finish | Brilliant |
| Quantity per set | Set of 10 |
| Sale per indivisible quantity | 1 |
| Connections - terminals | Pre-wired cable |
| Material | Thermoplastic ABS-UV stabilised: centre plate Zamak: fixing frame |
| Height | 74.5 Mm |
| Width | 74.5 Mm |
| Depth | 220 Mm |
| Net weight | 0.069 Kg |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for storage | -5...50 °C |
| Ambient air temperature for operation | 5...45 °C |
| Standards | EN 50049 EN 50157 |
| IP degree of protection | IP2xC |
| IK degree of protection | IK02 |
| Environmental characteristic | Bleach UV resistant Liquid soap Oil Ammonia Window-cleaning fluid Petrol Alcohol Acetone |
| Environmental health and issues | Halogen free |

Offer Sustainability

| | |
|--------------------|---|
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Under investigation |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Product Life Status : **Commercialised**