



## Main

Range	New Unica
Product or component type	Audio/Video socket
Connector type	HDMI
Electrical circuit type	Audio/Video
Device presentation	Mechanism with zamak fixing frame
Colour tint	Beige (RAL 1013)
Type of packing	Flow-pack

## Complementary

Fixing mode	Screws or claws
Number of modules	2 modules
Surface finish	Glossy
Quantity per set	Set of 10
Sale per indivisible quantity	1
Connections - terminals	Pre-wired cable
Material	Zamak fixing frame Thermoplastic ABS-UV stabilised centre plate
Height	75 mm
Width	75 mm
Depth	220 mm
Product weight	0.069 kg

## Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 50049 EN 50157
IP degree of protection	IP2xC
IK degree of protection	IK02

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental characteristic	UV resistant Oil Alcohol Window-cleaning fluid Ammonia Petrol Acetone Liquid soap Bleach
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**