



### Main

Range	New Unica
Product or component type	TV/F-Type DATA socket
Device presentation	Mechanism with fixing frame
Colour tint	White (RAL 9003)

### Complementary

TV connector	F connectors
Path attenuation	Maximum 0.8 dB (5...862 kHz)
Number of modules	2 modules
Material	Mechanism cover : thermoplastic ABS-UV stabilised
Surface finish	Glossy
Surface treatment	Untreated
Fixing mode	Screw
Depth	38 mm
Width	75 mm
Height	75 mm
Product weight	0.11 kg
Ambient air temperature for operation	5...45 °C
Ambient air temperature for storage	-5...50 °C

### Environment

IK degree of protection	IK04
IP degree of protection	IP2xC
Environmental characteristic	Petrol Window-cleaning fluid Bleach Alcohol Oil Liquid soap Ammonia UV resistant Acetone
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**