



Main

Range	New Unica
Product or component type	TV socket
Device application	Media device support Communication
Device presentation	Mechanism with fixing frame
TV socket type	Individual
Colour tint	White (RAL 9003)
Condition of use	Indoor

Complementary

TV connector	Male IEC 9.52 mm
Device composition	Support ring
Path attenuation	1.5 DB TV signal
DC current flow	Yes
Number of modules	2 modules
Material	Zamak: fixing frame Thermoplastic ABS-UV stabilised: central plate
Surface treatment	Untreated
Surface finish	Glossy
Marking	Without marking
Device mounting	Flush
Fixing mode	Screws
Depth	35.5 Mm
Width	74.5 Mm
Height	74.5 Mm
Embedding depth	26.5 Mm

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-25...55 °C
Environmental characteristic	Acetone Petrol Bleach Window-cleaning fluid Alcohol Liquid soap Ammonia Oil UV resistant

Environmental health and issues	Halogen free
Standards	CE

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**