



Main

Range	New Unica
Product or component type	TV socket
Device application	Communication Media device support
Device presentation	Mechanism with fixing frame
TV socket type	Intermediate
Colour tint	Anthracite (RAL 7021)

Complementary

TV connector	Male IEC 9.52 mm
Device composition	Support ring
Path attenuation	11 DB TV signal47...2200 MHz 2 DB IN-OUT signal47...2200 MHz
DC current flow	Yes
Number of modules	2 modules
Material	Zamak: fixing frame Thermoplastic ABS-UV stabilised: central plate
Surface finish	Painted powder coated
Marking	Without marking
Device mounting	Flush
Fixing mode	Screws
Depth	35.5 Mm
Width	74.5 Mm
Height	74.5 Mm
Embedding depth	26.5 Mm

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-25...55 °C
Environmental characteristic	Oil UV resistant Bleach Alcohol Petrol Liquid soap Acetone Window-cleaning fluid Ammonia

Environmental health and issues	Halogen free
Standards	CE

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**