



### Main

Range	New Unica
Range of product	New Unica
Device application	Mounting
Product or component type	Mounting box
Product compatibility	Unica
Device presentation	Without frame
Number of modules	2 x 8 modules
Fixing mode	Claws Embedment
Colour tint	Translucid green

### Complementary

Device mounting	Flush
Cable entry	6 knock-outs 20 mm for diameter 6 knock-outs 25 mm for diameter 2 bottom cable entries 45 x 25 mm for size 20 mm for diameter 4 bottom cable entries 50 x 35 mm for size 25 mm for diameter
Fire resistance	850 °C @<= 30 s
Material	Separator : ABS (acrylonitrile butadiene-styrene) Box : PC Tower : PC
Depth	50 mm
Width	221 mm
Height	156 mm
Product weight	0.207 kg
Targeted channel	Professional
Main colour tint	Green

## Environment

IK degree of protection	IK04
Environmental characteristic	Alcohol Liquid soap Ammonia Oil Window-cleaning fluid Bleach UV resistant Acetone Petrol
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**