



Main

Range	Exiway
Product name	Exiway Class
Product or component type	Emergency light fitting
Device application	Lighting
Function	Self-test
Supply	Maintained
Number of batteries	1 x 6 V 2.5 Ah Ni-Cd (Nickel-Cadmium) battery
Colour	White
Light source	LED : 11 W
Light source colour	White

Complementary

Range compatibility	Remote control
[Ue] rated operational voltage	220...230 V at 50 Hz AC/DC
Power consumption in VA	Non-maintained : 5.6 VA Maintained : 14 VA
Power consumption in W	Non-maintained : 1.5 W Maintained : 6.7 W
Current consumption	24 mA
Electrical insulation class	Class II
Autonomy	2 h
Charging time	12 h
Luminous flux	Emergency condition : 260 lm
Type of glass	Mineral glass
Material	Housing : plastic Cover : glass
Device mounting	Surface wall Flush wall
Height	223 mm
Width	303 mm
Depth	51 mm
Product weight	1.69 kg

Environment

IP degree of protection	IP42
IK degree of protection	IK07
Ambient air temperature for operation	0...40 °C
Fire resistance	850 °C
Product certifications	IMQ CE
Standards	IEC 60695-2-10 EN/IEC 60598-2-22 EN/IEC 62471

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details- Go to CaP for more details
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End Of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**