

### Main

Range	Exiway
Product name	Exiway Smartled Dicube
Product or component type	Emergency light fitting
Device application	Lighting
Function	Addressable
Supply	Non-maintained
Number of batteries	1 x 6.4 V 1.5 Ah
Light source	LED : 10 x 0.3 W integral LED base

### Complementary

[Ue] rated operational voltage	230 V at 50/60 Hz
Power consumption in VA	0.3 VA
Power consumption in W	4.1 W
Electrical insulation class	Class II
Autonomy	3 h
Charging time	24 h
Luminous flux	180 lm
Type of glass	Serigraphed transparent glass
Device mounting	Flush Wall Ceiling
Height	300 mm
Width	127 mm
Depth	45.5 mm
Product weight	0.65 kg

### Environment

IP degree of protection	IP65
Ambient air temperature for operation	0..40 °C
Fire resistance	850 °C
Product certifications	ENEC
Standards	EN 60598-2-2 EN 62034

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1707 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Product Life Status : **Commercialised**